

PORTABLE, TWO AXIS SHAPE MACHINE CUTS IN ALL POSITIONS





The MDS Programmable Shape Machine is a two-axis machine that runs on a track and carries a torch on a motorized cross-arm. It can be used for flame cutting, plasma cutting or welding a variety of shapes which are programmed and stored in memory. The system can be configured to run on all types of Bug-O rail. It is held in position with either powerful permanent magnets or vacuum cups, depending on the work material. This enables you to take the machine to the work, which will help reduce your material handling.

An optional computer software program is available. With this program you can select pre-programmed shapes or create your own custom shapes, and store and edit any number of them on disk. Selected shapes can then be downloaded to the machine as needed.

The machine has storage capacity in memory for 20 different programmed shapes. All programming is done with the provided handheld terminal. The terminal can be plugged into the connector on the rear of the machine or unplugged at any time. The terminal is not needed to run the machine once programmed.

Shapes and patterns are built up using segments. To do this, select the type of segment you want and determine what quadrant it is in – type it into the terminal. Any given shape can have up to 50 segments. Other functions such as weld/oxygen/plasma, on/off, time delay, or repeat a shape a number of times, also count as one segment each, if used.

Handheld Terminal Functions:

The programming operation is selected by pressing keys A, B, C, D, or E.


A: <u>ALL SEGMENTS</u>: Data entry for new shape consists of total number of segments and data for each segment.

B: PROGRAM SEGMENT: Press B on terminal to re-program a single segment. This is useful if there is an error in data for just one segment, so that the whole shape does not have to be re-entered.


C: <u>CHANGE SHAPE NUMBER</u>; Press $\underline{\mathbf{C}}$ on terminal to change the current shape number. The program switches to the new number in memory, and to whatever shape is stored there.

D: DISPLAY SHAPE DATA; Press $\underline{\mathbf{D}}$ to display the data for the current shape. The terminal display shows a total number of segments, and data for each segment one by one each time you press enter.

E: END OF SEGMENT SLOWDOWN; Press $\underline{\mathbf{E}}$ to set value of deceleration for the shape, when the machine approaches the end of each segment. This is useful when the shape has sharp corners to prevent overshoot. $\underline{99}$ is maximum slowdown, $\underline{\mathbf{0}}$ is no slowdown.



The different types of segments that can be loaded into the machine are as follows:



Other functions besides the moves shown above are: Weld Contact/Solenoid On/Off, Pause, Delay, Repeat another shape, Full ellipse, and Rapid Traverse.



Carriages

For Rigid and Semi-Flex rail



MPD-1065 4-Wheel Carriage Releasable, can be installed or released in any position anywhere on the rail.

For Ring Rail



BUG-5910 Ring Rail Carriage 4 wheels can be adjusted to the required ring diameter. Releasable.


For Hi-Flex Rails



FMD-1105 Hi-Flex Carriage Runs on high flex rail as shown below. Releasable.

Rails

The above shown carriages can be used on the rails shown below:



ARR-1080 8' (2.4 m) HD-Rigid Aluminum Rail

ARR-1085 4' (1.2 m) HD-Rigid Aluminum Rail




AFR-3000 8' (2.4 m) Semi-Flex Aluminum Rail




Ring Rails Diameter
BRR-1210-20 (20" 508 mm)
BRR-1210-27 (27" 685 mm)
BRR-1210-34 (34" 865 mm)
BRR-1210-41 (41" 1041 mm)
BRR-1210-48 (48" 1219 mm)

Custom sizes are available.



FMD-1050 Hi-Flex Rail Length = 5' (1.5 m) R - Minimum Radius 30" (762 mm)

Magnet Bars and Vacuum Bars



ARM-2325 Magnet w/Release




ARM-2425 Magnet w/Release



ARM-2380 ASupport Bar with Screw Feet S



ARM-2480 Support Bar with Screw Magnet Feet



FMD-2325 Magnet w/Release



ARM-2010 Rare Earth On/Off Magnet



AFR-2010 Rare Earth On/Off Magnet



ARM-2580 Support Bar with R.E. On/Off Magnets



FMD-2010 Rare Earth On/Off Magnet



ARV-1080/1085 Vacuum System



ARV-1240-__ Vacuum Support System



FMD-1220/1230 Vacuum System

Note: Refer to our MDS brochure (LIT-MDS-BRO), pages 8-9 for additional information.



MDS / STRAIGHT LINE / PROGRAMMABLE SHAPE PLASMA CUTTING / WELDING KIT MDS-4500 (120 VAC)




MDS-4502 (240 VAC)

Same as MDS-4500 except with: 1 MPD-1002 Master Drive Unit, 240 VAC

MDS-4504 (42 VAC)

Same as MDS-4500 except with: 1 MPD-1004 Master Drive Unit, 42 VAC

MDS / STRAIGHT LINE / PROGRAMMABLE OXY-FUEL CUTTING KIT



MDS-4552 (240 VAC)

Same as MDS-4550 except with:

1 MDS-1172 240 VAC MDS Solenoid Kit
1 MPD-1002 Master Drive Unit, 240 VAC


MDS-4554 (42 VAC)

Same as MDS-4550 except with:

1 MDS-1174 42 VAC MDS Solenoid Kit
1 MPD-1004 Master Drive Unit, 42 VAC



MDS / HI-FLEX / PROGRAMMABLE SHAPE PLASMA CUTTING / WELDING KIT FMD-4500 (120 VAC)



FMD-4502 (240 VAC)

Same as FMD-4500 except with: 1 MPD-1002 Master Drive Unit, 240 VAC

FMD-4504 (42 VAC)

Same as FM-4500 except with: 1 MPD-1004 Master Drive Unit, 42 VAC

MDS / HI-FLEX / PROGRAMMABLE SHAPE OXY-FUEL CUTTING KIT

FMD-4550 (120 VAC) 2 FMD-2170 Hi-Flex Rail w/ (8) FMD-2010 R.E. On/Off Magnets Torch Holder Assembly BUG-5188 BUG-6050 Hand Held Terminal MDS-1165 Shape Control Module 120 VAC MDS Solenoid Kit MDS-1170 MPD-1000 Master Drive Unit. 120 VAC MPD-1035 Handle w/ Cable Anchor FMD-1105 Hi-Flex Carriage WPD-1100-40 Linear Weaver w/ 40" (1 m) Long Arm

FMD-4552 (240 VAC)

Same as FMD-4550 except with:

1 MDS-1172 240 VAC MDS Solenoid Kit
1 MPD-1002 Master Drive Unit, 240 VAC

FMD-4554 (42 VAC)


Same as FMD-4550 except with:

1 MDS-1174 42 VAC MDS Solenoid Kit
1 MPD-1004 Master Drive Unit, 42 VAC





BUG-6220 Wireless serial connection set for use with PC Option software



Technical Data:

Power Requirements: 120 VAC / 50-60 Hz / 1 Ph

240 VAC / 50-60 Hz / 1 Ph

42 VAC / 50-60 Hz / 1 Ph

5-100 ipm (127-2540 mm/min) 2. BUG-6240 CAD Interface **Travel Speed:**

Net Weight of Kit: 45 lbs. (20.41 kg)

Cross Travel: 24" (610 mm)

Max. Line Segment


Dimension: 72" (1828 mm)

Within Limits of Travel

Min. Increment

.01" (0.3 mm) **Dimension:**

Delay Increment: .01 seconds



Computer Software

The MDS-Programmable Shape Machine can be programmed from a PC, using either of two software packages described below. Shapes can be created offline, and downloaded to the machine when required. A cable is supplied to connect to the serial port of the PC.

1. PC Option / BUG-6140

This runs under Windows, and allows you to:

- · Create shapes on the PC.
- Save any number of shapes to disk, and retrieve them as necessary.
- View a programmed shape on screen which helps program verification.
- Download programmed shapes from the PC to the machine.

This is a complete package that includes both the PC option and DeskCNC. This will allow you to take 2 dimensional CAD drawings and convert them to Shape files that you can directly load into your shape machine.

- DeskCNC is used to modify 2 dimensional CAD drawings (.DXF files) and create a toolpath
- The toolpath is saved as a shape file using DeskCNC
- The shape file can be loaded in the PC option for easy integration with the shape machine